

CARTCOMPLIANCE

ANSI/AAMI ST79 section 6.3(1)

 Care and handling of contaminated reusable items at the point of use. Immediate containment and transportation to the decontamination area is ideal so that the cleaning process can start as soon as possible before biofilms (accumulated biomass of bacteria and extracellular material that is tightly adhered to a surface and cannot be removed easily) start to form.

ANSI/AAMI ST79 section 6.4(1)

 Containment. The objective is to avoid cross contamination to either people or the environment. Place contaminated instruments in a puncture-resistant, leak-proof, closable and labelled container to avoid punctures to the container or your skin.

CDC IV.E.1. 18, 739, 975. Cat. IB/IC

 Establish policies and procedures for containing, transporting, and handling patient-care equipment and instruments/devices that may be contaminated with blood or body fluids

OSHA 1910.1030(g)(1)(i)(B)

 Contaminated materials that are to be decontaminated at a site away from the work area shall be placed in a durable, leak-proof, labeled or color-coded container that is closed before being removed from the work area. Warning labels shall be affixed to containers of regulated waste, refrigerators and freezers containing blood or other potentially infectious material; and other containers used to store, transport or ship blood or other potentially infectious materials

Elite Cart Covers transfer to Decontam TIPs **Hospital Logo** Transformative Information Panels GENERAL HOSPITAL **Department** -EADY DR Washable PEDIGO THORITY Durable hvdrophobic material



Pedigo's Elite Cart Covers ensure that compliancy standards are met and maintained while safely transporting and communicating the cart and its contents from destination to destination. Durable, long lasting cart covers may be customized with the logo, department designation or text.

Made from Polyester

- Polyester is a hydrophobic material that naturally repels liquids
- Able to handle the higher temperatures associated with commercial cleaning and drying
- Maintains its structure after being laundered
- Light weight
- Durable

Embedded Print Graphics

- No graphic peeling
- Color-fast
- Re-create hospitals logos perfectly onto Cart Cover
- Over 1100 stock colors available
- Unlimited graphics

Material Selection

- Standard (300 Denier)
- Fire Rated (500 Denier)
- Super Duty (915x1220)

Transformative Information Panels (TIP's) Patent Pending

- Highly visable biohazard indicator
- Integrated into the cover design
- Easily determine cart designation (OR, ER, food, etc.)

Base Band Patent Pending

- Allows cover to fit snug to cart and remain in place during use
- Allows cart cover to expand at the top without pulling up and exposing bottom of cart
- Prevents wheel well interference

Unique Features

- Extend cover above the cart top (6" to 12")
- Customization (graphics, logos, pockets, Cut Outs, Windows, Heights extension)

Warranty Information

• One year warranty

Made in the USA



PEDIGO

DR